

## **Liebherr's L538 Wheel Loader to be featured at the 2016 World of Concrete trade show**

- Highly versatile machine
- Increased productivity with Liebherr Electronics
- High fuel economy

**Las Vegas (USA), February, 2, 2016 – Liebherr Construction Equipment Co., invites World of Concrete participants to get an up close look at the new L538 Wheel loader at the Las Vegas Convention Center, Central Hall, Booth # C6212.**

The L 538 on display features a Z-bar linkage for standard operations, achieves a tipping load straight of 22,485 lb (10,199 kg) at an operating weight of 29,000 lb (13,154 kg) and is driven by a 154HP (l) / 115 kW. This loader is equipped with a 3.14yd<sup>3</sup> (2.40 m<sup>3</sup>) quick hitch re-handling bucket with bolt on cutting edge.

### **Highly versatile machine**

The L538 wheel loader belongs to the new generation of mid-size range loaders, most commonly referred as utility size. These size loaders are highly versatile machines suitable for a multitude of applications. They can be used in a traditional capacity, to stockpile or move earth/materials, or can be used to handle all types of construction material through the use different attachments.

### **Increased productivity with Liebherr Electronics**

The implementation of energy efficiency technologies such as the hydrostatic drive combined with the Liebherr Power Efficiency system (LPE), optimizes the interaction between drive components. This system is able to adjust the performance and power for every working situation, enhancing the efficiency of the wheel loader and providing additional fuel savings up to 25%.

### **High Fuel Economy**

An additional contributing factor to fuel economy is the configuration of the machine and the positioning of its engine. The engine is used as natural counterweight. The

center point of gravity of the drive line components is behind the rear axle to avoid unnecessary additional counterweight. Less operating weight has to be carried around, therefore, less horse power is required. Subsequently, less fuel is consumed.

### **Captions**

liebherr-wheel-loader-l538.jpg

The Liebherr L538 wheel loader in operation, preparing and maintaining stockpile areas for loading into trucks, crushers, and/or plant hoppers.

### **Contact**

Ana Cabiedes

Marketing and Communications Manager

Phone: +1 757 928 2503

E-mail: [ana.cabiedes@liebherr.com](mailto:ana.cabiedes@liebherr.com)

### **Released by**

Liebherr Construction Equipment Co.

Newport News, VA (USA)

[www.liebherr.com](http://www.liebherr.com)