

### **Liebherr will present a number of new products from its extensive range of construction machines at Intermat 2018**

- Trade fair stand E6/B056 in the outdoor area is 4500 m<sup>2</sup>
- Several world premieres and product launches for the European market
- Exhibits from the ranges of earthmoving and material handling machines, special deep mining machines, tower cranes, mobile cranes, crawler cranes and concrete technology

**Paris (France), December 20<sup>th</sup> 2017 –Liebherr will exhibit a number of new products at stand E6/B056 on the open-air grounds at Intermat 2018's Villepinte exhibition centre in northern Paris. In addition to the launch of new products for the European market, Liebherr will also present some world premieres. Furthermore, visitors to the technology pavilion will be able to find out more about the latest digitisation solutions and the Liebherr Reman programme.**

The Liebherr Group will present a cross-section of the latest construction machine technology at Intermat 2018, taking place from the 23<sup>rd</sup> to the 28<sup>th</sup> of April in Paris. In the E6/B056 outdoor area, approximately 4500 m<sup>2</sup> in size, the manufacturer will present innovative highlights from the product ranges for earthmoving and material handling machines, special deep mining machines, tower cranes, mobile cranes, crawler cranes and concrete technology.

Liebherr will present its new series of stereoloaders to visitors at the trade fair stand. Two smaller Stereoloaders<sup>®</sup> will celebrate their world premiere at Intermat. The two larger Stereoloaders<sup>®</sup> – L 514 and L 518 – were launched last summer. The L 514 Stereo is suitable for communal services and road construction, and provides reliable assistance for a wide range of applications. The larger L 518, a completely new model in Liebherr's range of wheel loaders, is designed for industrial use, for instance with solid rubber tyres for recycling operations.

Another machine making its premiere is the A 914 Litronic wheeled excavator from emission stage IV, which is being presented for the first time at a trade fair. With an operating weight between 14,900 and 17,200 kg and an engine power of

105 kW/143 hp, the 914 Litronic adapts perfectly for both classic earthmoving and road, sewer and pipeline construction. The machine stands out on every construction site thanks to its high traction for rapid acceleration, as well as high load bearing capacities and digging forces.

The R 936 Compact crawler excavator will also be on display for the first time in France. It has an operating weight of approximately 35 tonnes and is ideal for use where space is limited, for example in urban construction sites.

Liebherr has reworked the successful 172 EC-B 8 Litronic flat-top crane and will present its successor to experts at Intermat 2018. The jib has been extended by 2.5 metres to 62.5 metres and enables even more accurate division. The 172 EC-B 8 Litronic now lifts 1800 kilograms at the jib head with a radius of 62.5 metres. The maximum load bearing capacity remains 8000 kg. The new flat-top crane will be presented on the new 16 EC tower system alongside the LiUP internal crane driver elevator.

Liebherr is also exhibiting the attractive Reman range in Paris using a remanufactured V12 diesel engine. This gives the construction machine operator the option to use used components that have been remanufactured in accordance with industrial standards as fully fledged spare parts.

### **Captions**

liebherr-intermat-2018.jpg

Liebherr trade fair stand at Intermat 2018

### **Contact**

Dr. Gerold Dobler

Corporate Communications

Phone: +49 (0) 7351 41-2814

E-mail: [gerold.dobler@liebherr.com](mailto:gerold.dobler@liebherr.com)

### **Published by**

Liebherr-International Deutschland GmbH

Biberach / Riss, Germany

[www.liebherr.com](http://www.liebherr.com)