

WSbl 4201

Wine storage fridge
GrandCru

← 60 →



1 Zone	Temp Protect Plus	Humidity Select	Fresh Air	Flex Fit	Vibrate Safe	LED	Touch Display	Door Lock	Self Closing Door
Easy Fill	Smart Device Ready								

Energy efficiency class	
Energy consump. in 365 days/24 h	76 / 0.208 kWh ¹
Max. No. of Bordeaux bottles 0.75 Ltr	141 ²
Total volume	267 l ³
Noise output / noise class	38 dB(A) / C
Climate rating	SN-T (+10 °C to +43 °C)
Frequency / voltage	50/60 Hz / 220-240 V~
Connection Rating	1.5 A
Door	Full door, black
Side walls	black
Exterior dimensions in cm (h / w / d)	128.4 / 59.7 / 76.3 ¹
Controls	
Type of Control	LC monochrome display in the door, touch electronic
	Digital temperature display
Alarm in case of malfunction	visual and acoustic
Door alarm	visual and acoustic
Child proof function	yes
Features	
Temperature zones	1
Temperature range	+5 °C to +20 °C
Adjustable cooling circuits	1
Forced air system	Convection cooling, fresh air supply via FreshAir activated charcoal filter
Interior light	LED ceiling lighting
Handle	Slimline handle, black
Interface	SmartDeviceBox: optional accessory
Shelf material	Adjustable beech wood shelves
Storage shelves	4
Door hinges	Reversible door hinging, right
Lock	mechanically retrofittable
EAN-Nr.	9005382243893

¹ To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 3.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.

² These models are only bound for storing wine. Maximum DIN norm bordeaux bottles capacity (0.75 l) as per norm NF H 35-124 (H: 300.5 mm, Ø 76.1 mm)

³ In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point.