

# UWTes 1672

Built-under multi-temperature wine fridge  
Vinidor

82-87



|         |                 |           |            |              |                |     |                  |
|---------|-----------------|-----------|------------|--------------|----------------|-----|------------------|
| 2 Zones | Humidity Select | Fresh Air | UV Protect | Vibrate Safe | Steel Interior | LED | Telescopic Rails |
|---------|-----------------|-----------|------------|--------------|----------------|-----|------------------|

|                                       |  |
|---------------------------------------|--|
| Type                                  | flush / Under-worktop appliance  |
| Energy efficiency class               |  |
| Energy consump. in 365 days/24 h      | 142 / 0.389 kWh  |
| Max. No. of Bordeaux bottles 0.75 Ltr | 34 <sup>1</sup>  |
| Total volume                          | 94 l <sup>2</sup>  |
| Noise output / noise class            | 38 dB(A) / C   |
| Climate rating                        | SN-ST (+10 °C to +38 °C)   |
| Frequency / voltage                   | 50 Hz / 220-240 V~   |
| Connection Rating                     | 0.8 A  |
| Door                                  | Glass door with stainless steel frame  |
| Aperture dimensions in cm (h / w / d) | 82-87 / 60 / min. 58   |
| <b>Controls</b>                       |  |
| Type of Control                       | MagicEye, key electronic<br>Digital temperature display for both wine zones    |
| Alarm in case of malfunction          | visual and acoustic  |
| Door alarm                            | acoustic   |
| Child proof function                  | yes  |
| <b>Features</b>                       |  |
| Temperature zones                     | 2  |
| Temperature range                     | +5 °C to +20 °C  |
| Adjustable cooling circuits           | 2  |
| Forced air system                     | Convection cooling, fresh air supply via FreshAir activated<br>charcoal filter |
| Interior light                        | LED lighting permanently on, dimmable  |
| Handle                                | Aluminium handle   |
| Shelf material                        | Beech wood fittings  |
| Storage shelves                       | 5  |
| Pull-out shelves on telescopic rails  | 3  |
| Door hinges                           | Reversible door hinging, right   |
| Lock                                  | fitted   |
| EAN-Nr.                               | 9005382279472  |

<sup>1</sup> These models are only bound for storing wine. Maximum DIN norm bordeaux bottles capacity (0.75 l) as per norm NF H 35-124 (H: 300.5 mm, Ø 76.1 mm)

<sup>2</sup> In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point.