



# IECEX Certificate of Conformity

## INTERNATIONAL ELECTROTECHNICAL COMMISSION IEC Certification System for Explosive Atmospheres

for rules and details of the IECEx Scheme visit [www.iecex.com](http://www.iecex.com)

Certificate No.: **IECEX EPS 21.0047X** Page 1 of 4 Certificate history:  
Status: **Current** Issue No: 1 Issue 0 (2021-10-25)  
Date of Issue: 2024-10-10  
Applicant: **Liebherr-Mischtechnik GmbH**  
Im Elchgrund 12  
88427 Bad Schussenried  
**Germany**  
Equipment: **Water content sensor type Litronic WMS II - planar sensor P45-GD/P78-GD / rod sensor P45-GD**  
Optional accessory:  
Type of Protection: **Intrinsic safety "i", flameproof enclosure "d", protection by enclosure "t"**  
Marking: Ex db/ia IIC T4 Ga/Gb  
Ex tb/ia IIIC T135°C Da/Db

Approved for issue on behalf of the IECEx  
Certification Body:

Position:

Signature:  
(for printed version)

Date:  
(for printed version)



1. This certificate and schedule may only be reproduced in full.
2. This certificate is not transferable and remains the property of the issuing body.
3. The Status and authenticity of this certificate may be verified by visiting [www.iecex.com](http://www.iecex.com) or use of this QR Code.



Certificate issued by:

**Bureau Veritas Consumer Products Services Germany GmbH**  
Businesspark A96  
86842 Türkheim  
**Germany**





# IECEX Certificate of Conformity

Certificate No.: **IECEX EPS 21.0047X**

Page 2 of 4

Date of issue: 2024-10-10

Issue No: 1

Manufacturer: **Liebherr-Mischtechnik GmbH**  
Im Elchgrund 12  
88427 Bad Schussenried  
**Germany**

Manufacturing  
locations:

This certificate is issued as verification that a sample(s), representative of production, was assessed and tested and found to comply with the IEC Standard list below and that the manufacturer's quality system, relating to the Ex products covered by this certificate, was assessed and found to comply with the IECEX Quality system requirements. This certificate is granted subject to the conditions as set out in IECEX Scheme Rules, IECEX 02 and Operational Documents as amended

## STANDARDS :

The equipment and any acceptable variations to it specified in the schedule of this certificate and the identified documents, was found to comply with the following standards

- IEC 60079-0:2017 Explosive atmospheres - Part 0: Equipment - General requirements  
Edition:7.0
- IEC 60079-1:2014 Explosive atmospheres - Part 1: Equipment protection by flameproof enclosures "d"  
Edition:7.0
- IEC 60079-11:2011 Explosive atmospheres - Part 11: Equipment protection by intrinsic safety "i"  
Edition:6.0
- IEC 60079-26:2014 Explosive atmospheres – Part 26: Equipment with Equipment Protection Level (EPL) Ga  
Edition:3.0
- IEC 60079-31:2013 Explosive atmospheres - Part 31: Equipment dust ignition protection by enclosure "t"  
Edition:2

This Certificate **does not** indicate compliance with safety and performance requirements other than those expressly included in the Standards listed above.

## TEST & ASSESSMENT REPORTS:

A sample(s) of the equipment listed has successfully met the examination and test requirements as recorded in:

Test Report:

DE/EPS/ExTR21.0049/01

Quality Assessment Report:

DE/EPS/QAR20.0013/03



# IECEx Certificate of Conformity

Certificate No.: **IECEx EPS 21.0047X**

Page 3 of 4

Date of issue: 2024-10-10

Issue No: 1

## EQUIPMENT:

Equipment and systems covered by this Certificate are as follows:

The water content sensor type Litronic-WMSII is used to measure the water content in liquids and bulk solids in potentially explosive areas. It consists of a stainless steel carrier with built-in stray field capacitor including intrinsically safe sensor electronics and interface electronics in the transmitter head. Simple equipment such as a customer-specific flange for the rod sensors or a screw-in and weld-on flange for the planar sensors are used for assembly.

The stainless steel carrier with the stray field capacitor is installed in the hazardous area of category 1. The mounting flange is installed in the partition wall, which separates the areas in which equipment of category 1 or 2 is required.

Supply voltage:  $U_n = U_m = 12 \text{ VDC}$  (SELV/PELV)

## SPECIFIC CONDITIONS OF USE: YES as shown below:

The flameproof joints are not intended to be repaired.

Build-up of electrostatic charge on the painted enclosure shall be avoided. High charge generating processes shall be excluded.

Maximum ambient temperature range :

Sensor-head: -20 °C to +80 °C

Transmitter-head: -20 °C to +70 °C

Maximum process temperature at Sensor: -20 °C to +80 °C



# IECEX Certificate of Conformity

Certificate No.: **IECEX EPS 21.0047X**

Page 4 of 4

Date of issue: 2024-10-10

Issue No: 1

**DETAILS OF CERTIFICATE CHANGES (for issues 1 and above)**  
Change of electrical data