

Maschinenportfolio

Alle im Crane Planner 2.0 integrierten Maschinen auf einen Blick

LTM/LRT/LTC Mobilkrane	LR/LTR Raupekrane	HS Seilbagger
LTM 1750-9.1 (800t)	 LR 1400 SX	 HS 8300.2
LTM 1750-9.1	 LR 1300.2 SX unplugged	 HS 8300.1
LTM 1650-8.1	 LR 1300.1 SX	 HS 8200
LTM 1450-8.1	 LR 1250.1 (unplugged)	 HS 8130.1
LTM 1350-6.1	 LR 1200.1 (unplugged)	 HS 8100.2
 LTM 1300-6.3	 LR 1160.1 (unplugged)	 HS 8100.1
LTM 1300-6.2	 LR 1130.1 (unplugged)	 HS 8070.1
LTM 1250-5.1	 LR 1100.1	 HS 8040.1
LTM 1230-5.1	 LTR 1150	 HS 8300 *
LTM 1160-5.2	 LR 1300 SX *	 HS 8130 *
 LTM 1150-5.3	 LR 1300 *	 HS 8100*
 LRT 1130-2.1	 LR 1280 *	 HS 8030*
LTM 1120-4.1	 LR 1250 *	
 LTM 1110-5.2	 LR 1200 SX*	
 LTM 1100-5.3	 LR 1200 *	
LTM 1090-4.2	 LR 1160 *	
 LTC 1050-3.1E (e-Motor)	 LR 1130 *	
LTC 1050-3.1 (Seilausleger)	 LR 1110 *	
LTC 1050-3.1 (Telematik)	 LR 1100 *	
		MK Mobilbaukrane
		 MK 120-5.1E



Exklusiv im Crane Planner 2.0

* Pro Version erforderlich