
Technical Description Rail Mounted Gantry Cranes



LIEBHERR

Technical Data



RMG Model Designation



Typical RMG Mod	del Range*
A: Gantry span	22 - 70 m
B: Lifting Height	From 9.2 m for 1 over 2
	Up to 26.9 for 1 over 8
C: Cantilever	0 - 20 m
D: Cantilever	0 - 20 m
E: Travel wheel gauge	16.5 m - 18.2 m
F: Buffer to buffer	23.2 m - 25.5 m
G: Wheel spacing	1 m - 2 m dependant on wheel loads
Wheels per corner	6 - wide leg
	4 - narrow leg
SWL	40.6 - 50 t single 50 - 65 t twin

Typical Design Parameters*


*Other features and dimensions also available

Classification according to F.E.M.	U7-Q2-A7 (Single lift)
In service wind speed	72 km/h (20 m/s)
Out of service wind speed	151.2 km/h (42 m/s)
Ambient temperature range	-45°C to + 45°C

Working Speeds**

9 1	
Hoisting with no load	56 m/min
Hoisting with rated load	28 m/min
Trolley travel (with and without load)	70 m/min
Gantry travel without load	130 m/min
Slewing ± 190° (optional)	1.2 RPM

**Higher speeds also available on request



Advantages of RMG for Yard Stack-

- Suitable for both port and rail terminals.
- Suitable for various yard space conditions.
- Increased yard capacity with wider and higher stack possibilities.
- Reduction in emissions and noise.
- Minimal maintenance.
- Electric supply for energy efficiency and reduced running costs.



Liebherr Anti-Sway System (Eight Rope Reeving)





Advantages by Design

- Minimal spreader positioning times.
- No-sway in hoist, trolley and travel directions.
- Anti-skew.
- No additional ropes or devices necessary.
- No head block Reduced rope load and tare weight.
- Lower energy consumption.
- All electric spreader Less maintenance.
- Significant increase in productivity when compared with alternative designs.

Motors and Speed Control System



Motors/Suppliers

- All drives are sized for maximum torque and power requirements, guaranteeing extended lifetime.
- All major components are sourced from reputable european manufacturers.

Speed Control System

- The control system used has been specifically developed for container cranes by Liebherr, which has resulted in a flexible, robust construction with exceptional reliability.
- The "plug-in" modular construction of the electronic equipment is designed to maximise crane availability and minimise the necessity for highly skilled electronic personnel.

Liebherr Rail Mounted Gantry Crane

- Liebherr reeving system: Sway prevention, not sway correction.
- Regeneration during lowering of load and drive deceleration, results in overall reduction in power consumption.
- Electric (gantry align) steering.
- Rigid robust structure Optimum for automation. Optional DGPS auto steering and container positioning.
- Direct gearbox driven travel systems.
- Separate drives for hoist, travel and trolley, with no need for side shift on the spreader. Allows superior fine positioning with simultaneous motion.

- Worldwide Liebherr service network.
- Extensive training (in-house and on-site).
- Purpose built state-of-the-art design and production facilities located in Ireland since 1958.
- Highly skilled and experienced employees with expertise inhouse for after sales service.
- Responsibility with Liebherr, eliminating interface and compatibility problems (i.e. structural, mechanical and electrical design, production, commissioning and service).

Options

- · Rotating machinery trolley.
- Interface with TOS (terminal operating system).
- Trim and skew spreader positioning.
- Energy chain/festoon system.
- Non-contact anti-collision system.

- Automation of RMG and container tracking.
- Container positioning system.
- Remote operation option.
- Fault data between crane and office by RF link/Fibre optic with optional link to the Liebherr factory.

Diagnostic and Managment System

Description

- · Liebherr designed and built.
- Windows OS with CoDeSys logic control system.
- Status of switchgear and external electrical components.
- Stores up to 20,000 faults.
- User-friendly interface with easy to use colourful screens.
- Independence of crane logic system, therefore does not interfere with crane control in the event of self failure.
- Includes trending and tables for production data and drive data.

Summary of Main System Features

- General Control Overview.
- "Crane ON" status.
- Individual Drive ON screens (one for each drive).
- Detailed drive data (motor current, voltage, speed).
- Wind speed and history.
- · Spreader status.
- · Fault stack.
- · Load statistics.
- Maintenance.

